

Representative Image

Catalog No. TL24415R

Description: MLO 150A 24CRT 3P4W 208Y/120V 3R

UPC No 783164190175

Home > Load Center & Meter Combos > Load Centers

Main lug load centers can be used as a home's main panel or sub panel depending upon your preferences. All ABB load centers are rated up to 60 degree/75 degree centrigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TL24415R features space for 24, 1" breakers, 3 phases, a 150 A bus ampere rating, and an outdoor suitable enclosure.

Descriptors

Category	Load Centers
GO Schedule	R7

Specifications

1" Space	24
1/2" Space	0
Amperage	150 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	208Y/120V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 3R
Phase	3 Phase
Service & Voltage	3 Phase, 4 Wire, 208Y/120V ac
Wires	4 Wire

Classifications

UL/CUL Listing	UL