



Image représentative

n° de catalogue TL270SCU

Description: 2 CIRC 70A INDOOR SURFACE

UPC No 783164275490

Accueil > Load Centers > Load Centers

Main lug load centers can be used as a home's main panel or sub panel depending upon your preferences. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TL270SCU features space for 2, 1" breakers, a 70 A bus ampere rating, a copper bus, and a surface enclosure.

Descripteurs

Catégorie	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Spécifications

1" Space	2
1/2" Space	4
Amperage	70 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	No
Enclosure	Indoor
Enclosure Type	Indoor, Surface Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
Cote NEMA	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----