



**Catalog No. TL30420R**

**Description: MLO 200A 30CRT 3P4W 208Y/120V 3R**

**UPC No 783164190182**

**Home > Load Centers > Load Centers**

Main lug load centers can be used as a home's main panel or sub panel depending upon your preferences. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TL30420R features space for 30, 1" breakers, 3 phases, a 200 A bus ampere rating, and an outdoor suitable enclosure.

**Descriptors**

|             |              |
|-------------|--------------|
| Category    | Load Centers |
| GO Schedule | R7           |

**Specifications**

|                              |                               |
|------------------------------|-------------------------------|
| 1" Space                     | 30                            |
| 1/2" Space                   | 0                             |
| Amperage                     | 200 A                         |
| Circuit Breaker Style        | Plug-In                       |
| Device type                  | Main Lug                      |
| Door                         | Yes                           |
| Enclosure                    | Outdoor                       |
| Enclosure Type               | Outdoor, Surface Mount        |
| Factory Installed Ground Kit | No                            |
| Feed                         | Either                        |
| Input/Output Voltage         | 208Y/120V ac                  |
| Interrupting Capacity Rating | 65                            |
| Load Center Type             | Standard                      |
| NEMA Rating                  | NEMA 3R                       |
| Phase                        | 3 Phase                       |
| Service & Voltage            | 3 Phase, 4 Wire, 208Y/120V ac |
| Wires                        | 4 Wire                        |

**Classifications**

|                |    |
|----------------|----|
| UL/CUL Listing | UL |
|----------------|----|