



Representative Image

Catalog No. TLM1212RCU

Description: FLD CNVRTB 125A 12CRK 22K IC 3R

UPC No 783164112931

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM1212RCU features space for 12, 1" breakers, a 125 A bus ampere rating, a copper bus, and an outdoor suitable enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

1" Space	12
1/2" Space	24
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 3R
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----

Publications

Title	Publication No.	Publication Type
PowerMark Gold* Load Centers: 100-125 Amps, 12/22/24 Circuits, Outdoor 2 pages.	DET-800	Brochures

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.