



Representative Image

Catalog No. TLM2412CCU

Description: FLD CNVRTB 125A 24CRK 22K IC COMB

UPC No 783164112320

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM2412CCU features space for 24, 1" breakers, a 125 A bus ampere rating, a copper bus, and a combination/flush enclosure.

Descriptors

| | |
|-------------|--------------------|
| Category | Load Centers |
| GO Schedule | RD |
| Grouping | Single Phase - USA |

Specifications

| | |
|------------------------------|------------------------------|
| # Branch Circuit 250A | 24 |
| 1" Space | 24 |
| 1/2" Space | 0 |
| Amperage | 125 A |
| Circuit Breaker Style | Plug-In |
| Device type | Main Lug |
| Door | Yes |
| Enclosure | Indoor |
| Enclosure Type | Indoor, Combination |
| Factory Installed Ground Kit | No |
| Feed | Either |
| Input/Output Voltage | 120/240V ac |
| Interrupting Capacity Rating | 65 |
| Load Center Type | Standard |
| NEMA Rating | NEMA 1 |
| Phase | 1 Phase |
| Service & Voltage | 1 Phase, 3 Wire, 120/240V ac |
| Wires | 3 Wire |

Classifications

| | |
|----------------|----|
| UL/CUL Listing | UL |
|----------------|----|

Dimensions

| | |
|--------|---------|
| Depth | 3.7 in |
| Height | 24.7 in |

by ABB

Dimensions

| | |
|--------|---------|
| Weight | 24.5 lb |
| Width | 14.0 in |