

Representative Image

Catalog No. TLM2412CCU

Description: FLD CNVRTB 125A 24CRK 22K IC COMB

UPC No 783164112320

Home > Load Center & Meter Combos > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centrigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM2412CCU features space for 24, 1" breakers, a 125 A bus ampere rating, a copper bus, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	24
1" Space	24
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL

Dimensions

Height	24.7 in
Weight	24.5 lb

Dimensions	
Width	14.0 in