



Representative Image

Catalog No. TLM2412CCUG

Description: 125A CONV LC 24-24CRT N1 W/GRND

UPC No 783164471953

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM2412CCUG features space for 24, 1" breakers, 125 A bus ampere rating, a copper bus, a factory installed ground bar, and a combination/flush enclosure.

Descriptors

Category	Load Centers
Grouping	Single Phase - USA

Specifications

1" Space	24
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Surface Mount
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	1 Phase

Classifications

UL/CUL Listing	UL
----------------	----