



Image représentative

n° de catalogue TLM612FCUD

Description: 6CIRC MNLUG 125A INDOOR FLUSH W/DR

UPC No 783164267990

Accueil > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM612FCUD features space for 6, 1" breakers, a 125 A bus ampere rating, a copper bus, an optional door for 6-8 circuit panel, and a flush enclosure.

Descripteurs

Catégorie	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Spécifications

1" Space	6
1/2" Space	12
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Flush Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
Cote NEMA	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----