



Representative Image

## Catalog No. TLM812FCUD

**Description:** 8 CIRC MNLUG 125A INDOOR FLUSH W/DR

**UPC No** 783164268041

**Home > Load Centers > Load Centers**

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM812FCUD features space for 8, 1" breakers, 125 A bus ampere rating, a copper bus, an optional door for 6-8 circuit panel, a factory installed ground bar, and a surface enclosure.

### Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

### Specifications

1" Space	8
1/2" Space	16
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Flush Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

### Classifications

UL/CUL Listing	UL
----------------	----