

Representative Image

Catalog No. TLM812FCUD

Description: 8 CIRC MNLUG 125A INDOOR FLUSH W/DR

UPC No 783164268041

Home > Load Center & Meter Combos > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centrigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM812FCUD features space for 8, 1" breakers, 125 A bus ampere rating, a copper bus, an optional door for 6-8 circuit panel, a factory installed ground bar, and a surface enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

1" Space	8
1/2" Space	16
Amperage	125 A
Circuit Breaker Style	Plug-In
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Flush Mount
Factory Installed Ground Kit	No
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL