



Representative Image

Catalog No. TM1210RCU

Description: 100A 12CT 1P3W 120/240V 22K IC 3R

UPC No 783164113020

Home > Load Centers > Load Centers

PowerMark Gold main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM1210RCU features spaces for 12, 1" breakers, a 100 A bus ampere rating, a copper bus, and an outdoor suitable enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

1" Space	12
1/2" Space	24
Amperage	100 A
Circuit Breaker Style	Plug-In
Device type	Main Breaker
Door	No
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	Yes
Feed	Top
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
NEMA Rating	NEMA 3R
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----

Publications

Title	Publication No.	Publication Type
PowerMark Gold* Load Centers: 100-125 Amps, 12/22/24 Circuits, Outdoor 2 pages.	DET-800	Brochures

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.