



Representative Image

Catalog No. TM12410C

Description: 100A 12CRT 3P4W 208Y/120V 10K IC

UPC No 783164189964

Home > Load Centers > Load Centers

Main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM12410C features spaces for 12, 1" breakers, a 100 A bus ampere rating, 3 phases, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	R7

Specifications

1" Space	12
1/2" Space	0
Amperage	100 A
Circuit Breaker Style	Plug-In
Device type	Main Breaker
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	No
Feed	Top
Input/Output Voltage	208Y/120V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	3 Phase
Service & Voltage	3 Phase, 4 Wire, 208Y/120V ac
Wires	4 Wire

Classifications

UL/CUL Listing	UL
----------------	----