



Representative Image

Catalog No. TM30420R

Description: 200A 30CRT 3P4W 208Y/120V 10K IC 3R

UPC No 783164190250

Home > Load Centers > Load Centers

Main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM30420R features spaces for 30, 1" breakers, a 200A main ampere rating, 3 phases, and an outdoor suitable enclosure.

Descriptors

Category	Load Centers
GO Schedule	R7

Specifications

1" Space	30
1/2" Space	0
Amperage	200 A
Circuit Breaker Style	Plug-In
Device type	Main Breaker
Door	No
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	No
Feed	Top
Input/Output Voltage	208Y/120V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
NEMA Rating	NEMA 3R
Phase	3 Phase
Service & Voltage	3 Phase, 4 Wire, 208Y/120V ac
Wires	4 Wire

Classifications

UL/CUL Listing	UL
----------------	----