



Image représentative

n° de catalogue TM3220RCU

Description: 200A32CT 1P3W 120/240V 22K IC 3R

UPC No 783164113150

Accueil > Load Centers > Load Centers

PowerMark Gold main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM3220RCU features spaces for 32, 1" breakers, a 200 A bus ampere rating, a copper bus, and an outdoor suitable enclosure.

Descripteurs

Catégorie	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Spécifications

1" Space	32
1/2" Space	16
Amperage	200 A
Circuit Breaker Style	Plug-In
Device type	Main Breaker
Door	No
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	No
Feed	Top
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
Cote NEMA	NEMA 3R
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----