



Representative Image

Catalog No. TQ2140

Description: TQO 2 POLE RESI PLUG-IN 40 AMP

UPC No 783164083910

Home > Circuit Breakers > Residential Circuit Breakers > Q Line

The TQ2140 breaker is for use only in 'Square D' QO load centers. It features a 3/4" width, 2 poles, ampere rating of 40 A, interrupting rating of 10kAIC, and a voltage rating of 120/240V.

Descriptors

| | |
|-------------|--------|
| Category | Q Line |
| GO Schedule | RQ |

Specifications

| | |
|--------------------|---------------------|
| Specialty Breakers | Square D Compatible |
| Voltage | 120/240 V |
| Amperage | 40 A |
| Poles | 2 |
| GSA Compliance | No |