



Representative Image

Catalog No. TQB22Y100

Description: SWITCH 2P 100A

UPC No 783164189193

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. Y100 Amps 100 A

Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EB

Specifications

Frame Type	Q-Line
Amperage	100 A
System Voltage	120 Vac 120/240 Vac 240 Vac
Poles	2
Trip Function	Switch
Continuous Current Rated	Standard
120 Vac Interrupting Rating	5 KAIC
120/240 Vac Interrupting Rating	5 KAIC
240 Vac Interrupting Rating	5 KAIC
Suitable for Reverse Feed	Yes
Long Time	No
Protective Relays	No
Current Metering	No
GSA Compliance	No

Classifications

UL File #	E11592
-----------	--------