



Representative Image

## Catalog No. TQL70S

**Description: ENCLOSURE NEMA 1 SURFACE 70A**

**UPC No 783164022148**

**Home > Circuit Breakers > Circuit Breaker Enclosures**

Designed for outdoor rural dwellings and farm buildings to allow connection to a standby generator. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code. Non-fusible. 60/75 C conductor rating. Lockable handle in ON or OFF position. Galvanized steel construction. TQL70S

### Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

### Specifications

Enclosure Type	NEMA Type 1
Mounting	Surface
Frame Type	Q-Line
Amperage	70 A
Material	Steel
GSA Compliance	No

### Classifications

UL/CUL Listing	CSA UL
----------------	-----------

### Dimensions

Height	12.88 in
Width	5.75 in
Weight	6.1 lb