



Representative Image

Catalog No. TQL70S

Description: ENCLOSURE NEMA 1 SURFACE 70A

UPC No 783164022148

Home > Circuit Breakers > Circuit Breaker Enclosures

Designed for outdoor rural dwellings and farm buildings to allow connection to a standby generator. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code. Non-fusible. 60/75 C conductor rating. Lockable handle in ON or OFF position. Galvanized steel construction. TQL70S

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

Specifications

Enclosure Type	NEMA Type 1
Mounting	Surface
Frame Type	Q-Line
Amperage	70 A
Material	Steel
GSA Compliance	No

Classifications

UL/CUL Listing	CSA UL
----------------	-----------

Dimensions

Height	12.88 in
Depth	4.06 in
Width	5.75 in
Weight	6.1 lb