



Representative Image

Catalog No. TSMR820CSFLFMG

Description: MSLC MB Rgls 200A 8/16 S UGOH MEG

UPC No 783164415162

Home > Load Centers > Meter Socket Load Center

PowerMark Gold Meter Socket Load Centers are an ideal option for residential applications. Additionally, PowerMark Gold Meter Socket Load Centers provide increased reliability and maximum circuit layout flexibility. All our PowerMark Gold Meter Socket Load Centers are built with high-quality materials for extended durability. Furthermore, their perfected design allows for an easy and fast installation. The TSMR820CSFLFMG is a ringless, main breaker meter socket and features spaces for 8, 1" breakers, a 200A main ampere rating, Florida Meter Group Compatibility, and an outdoor suitable, surface enclosure.

Descriptors

Category	Meter Socket Load Center
GO Schedule	RB
Grouping	Meter Socket

Specifications

Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	200 A
Enclosure	Outdoor
1" Space	8
1/2" Space	16
Feed	Either
Door	Yes
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 3R
Factory Installed Ground Kit	Yes
Enclosure Type	OutdoorType 3R
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Width	14.0 in
-------	---------

by ABB