



Image représentative

## n° de catalogue TXQC32025WL

**Description:** CIRCUIT BREAKER 3P 25A

**UPC No** 783164099157

**Accueil > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories. 25WL Amps 25 A

### Descriptors

|              |                                   |
|--------------|-----------------------------------|
| Catégorie    | Q-Line Miniature Circuit Breakers |
| Product Line | Q-Line (Lug-Lug)                  |
| GO Schedule  | EB                                |

### Specifications

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Trip Style                      | Non-Interchangeable               |
| Frame Type                      | Q-Line                            |
| Amperage                        | 25 A                              |
| System Voltage                  | 120 Vac<br>120/240 Vac<br>240 Vac |
| Poles                           | 3                                 |
| Trip Function                   | LI                                |
| Continuous Current Rated        | Standard                          |
| 120 Vac Interrupting Rating     | 65 KAIC                           |
| 120/240 Vac Interrupting Rating | 65 KAIC                           |
| 240 Vac Interrupting Rating     | 65 KAIC                           |
| Suitable for Reverse Feed       | Yes                               |
| Long Time                       | Fixed                             |
| Instantaneous                   | Fixed                             |
| Protective Relays               | No                                |
| Current Metering                | No                                |
| Special Markings                | HACR                              |
| GSA Compliance                  | No                                |

### Classifications

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|