



Catalog No. TY527MX

Description: CBL TIE 120LB 13.4 UV BLACK

UPC No 786210805122

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie, Black Color Nylon 6.6, Length of 340.36mm (13.4 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.86mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), 50 Pack

Descriptors

| | |
|------------------|--|
| Category | Cable ties |
| Special Features | Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. |

Specifications

| | |
|------------------|--------------------------|
| Material | Nylon/Polyamide 6.6 |
| Color | Black |
| Lock Mechanism | Stainless Steel Barb |
| Tensile Strength | 120 pounds , 534 newtons |

Classifications

| | |
|------------|-----------|
| Brand Name | Ty-Rap |
| Standard | UL E49405 |

Dimensions

| | |
|-----------------|--------------------------|
| Width | 0.27 in , 6.9 mm |
| Length | 13.5 in , 343 mm |
| Thickness | 0.06 in , 1.5 mm |
| Bundle Diameter | Max 4.02 in , Max 102 mm |

Compliance and Certifications

| | |
|-------|-----------------------------|
| RoHS | RoHS3 Compliant |
| REACH | REACH 247 Compliant |
| TSCA | TSCA Section 6(h) Compliant |