



Catalog No. TYH25M

Description: CABLE TIE 50LB 7IN GR NYL HEAT STBL

UPC No 786210810973

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, Length of 185mm (7.3 Inches), Width of 4.7mm (0.18 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 48mm (1.89 Inches), Tensile Strength Rating of 220 Newtons (49 Pounds)

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Green
Lock Mechanism	Stainless Steel Barb
Tensile Strength	49 pounds , 220 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.18 in , 4.7 mm
Length	7.3 in , 185 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	Max 1.89 in , Max 48 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.7 mm
Length belt/tape/tie	185 mm
Length belt/tape/tie	7.28 inch

ETIM	EC000046 Cable tie
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	48 mm
Min. holding force	220 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	1349334_2014-11-06	N/A
UL	E49405	N/A	ZODZ	N/A	N/A