



Catalog No. UNF1005-GN

Description: PVC CTD UNF FEM UNION 4IN GREEN

UPC No 704508028640

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Explosion and Dust-Ignition Proof UNF Female Union, Pipe Size 4 Inch/103 Metric, 3 Piece, for Hazardous and Non-hazardous Locations, Overall Length 4.25 Inch/107.95 Millimeters, Overall Diameter 6.19 Inch/157.23 Millimeters, Electrogalvanized Steel, Green

Descriptors

Category	Electrical conduit coupling
Special Features	Compact Design Which Permits Assembly with a Minimum of Clearance to Other Adjacent Conduit and/or Equipment
Application	To Connect Conduit to Conduit, or to Provide a Means for Future Modification of the Conduit System

Specifications

Material	Steel
Color	Green

Classifications

Brand Name	Ocal
Standard	UL 1203, CSA

Dimensions

Trade Size	4 in , 103 mm
Outside Diameter	6.19 in , 157.23 mm
Length	4.25 in , 107.95 mm

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Other
Model	Thread
For nominal tube diameter	103 mm
Two piece	N
With inspection opening and cover	N

by ABB