



Catalog No. UNF205-GN

Description: PVC CTD UNF FEM UNION 3/4IN GREEN

UPC No 704508028626

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Explosion and Dust-Ignition Proof UNF Female Union, Pipe Size 3/4 Inch/21 Metric, 3 Piece, for Hazardous and Non-hazardous Locations, Overall Length 2.13 Inch/54.10 Millimeters, Overall Diameter 1.81 Inch/45.97 Millimeters, Electrogalvanized Steel, Green

Descriptors

Category	Electrical conduit coupling
Special Features	Compact Design Which Permits Assembly with a Minimum of Clearance to Other Adjacent Conduit and/or Equipment
Application	To Connect Conduit to Conduit, or to Provide a Means for Future Modification of the Conduit System

Specifications

Material	Steel
Color	Green

Classifications

Brand Name	Ocal
Standard	UL 1203, CSA

Dimensions

Trade Size	3/4 in , 21 mm
Outside Diameter	1.81 in , 45.97 mm
Length	2.13 in , 54.1 mm

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Other
Model	Thread
For nominal tube diameter	21 mm
Two piece	N
With inspection opening and cover	N

by ABB