



Representative Image

Catalog No. XJG34-G

Description: EXP CPLG 1IN, LENG 10IN GRAY

UPC No 704508417574

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated XJG Rigid Conduit Expansion Coupling with Internal Bonding Jumper, 1 Inch/27 Metric, Body is Malleable Iron with Zinc Plating, Internal Bonding Jumper is Tinned Copper Braid, Packing PTFE/Synthetic Fiber Material, 4 Inch/101.60 Millimeters Movement, Diameter 2.67 Inch/67.82 Millimeters, Length 10.00 Inch/254.00 Millimeters, Height 2.99 Inch/75.95 Millimeters, Gray

Descriptors

Category	Electrical conduit coupling
Special Features	No Disassembly Necessary to Install
Application	Allows for the Contraction and Expansion of a Conduit Run Without Reducing the Mechanical or Bonding Integrity of the Raceway

Specifications

Material	Iron with Zinc Plating
Color	Gray

Classifications

Brand Name	Ocal
Standard	UL E23018

Dimensions

Trade Size	1 in , 27 mm
Outside Diameter	2.67 in , 67.82 mm
Length	10 in , 254 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Surface protection	Other
Model	Thread

by ABB

ETIM	EC000939 Coupler for installation tubes
For nominal tube diameter	27 mm
With inspection opening and cover	N