



Representative Image

Catalog No. XJG68-GN

Description: EXP CPLG 2IN, LENG 15.25IN GREEN

UPC No 704508028657

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated XJG Rigid Conduit Expansion Coupling with Internal Bonding Jumper, 2 Inch/53 Metric, Body is Malleable Iron with Zinc Plating, Internal Bonding Jumper is Tinned Copper Braid, Packing PTFE/Synthetic Fiber Material, 8 Inch/203.20 Millimeters Movement, Diameter 3.86 Inch/98.04 Millimeters, Length 15.25 Inch/387.35 Millimeters, Height 4.18 Inch/106.17 Millimeters, Green

Descriptors

Category	Electrical conduit coupling
Special Features	No Disassembly Necessary to Install
Application	Allows for the Contraction and Expansion of a Conduit Run Without Reducing the Mechanical or Bonding Integrity of the Raceway

Specifications

Material	Iron with Zinc Plating
Color	Green

Classifications

Brand Name	Ocal
Standard	UL E23018, CSA

Dimensions

Trade Size	2 in , 53 mm
Outside Diameter	3.86 in , 98.04 mm
Length	15.25 in , 387.35 mm

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Surface protection	Other
Model	Thread
For nominal tube diameter	53 mm
With inspection opening and cover	N