

Representative Image

Ref. No. 673334 | Cat. No. EP101UCB10

Description: Miniature circuit breaker EP100UC 1P 10A B

EAN 5413656733348

Home > Modular DIN-rail devices > Circuit Protection > MCB DIN-rail

Descriptors

Category	MCB DIN-rail
Family	Circuit protection

Specifications

In (A)	10
Number of poles	1P
Number of modules	1
Curve Type	B (3-5 In)
Group	ElfaPlus
Range	Commercial - Industrial
Switch	EP100 UC : 6kA - AC/DC
Connections- Top	Screw
Connections- Bottom	Screw
Standards	10kA industrial BS EN 60947-2 6kA domestic BS EN 60898
AC/DC	AC/DC
Logo	GE
Rated voltage	230 V / 400 V
Short-circuit capacity (kA)	6
Selectivity class	3
Terminal capacity max (mm²)	25-35 mm²
Electrical service life	20000/10000
Minimum operating voltage Ubmin (V)	12 V
Terminal capacity min (mm²)	0.75 / 1 mm²
Tropicalisation	95%RH at 55°C

Classifications

Approvals	CE VDE
ETIM 5.0	EC000042 - Miniature circuit breaker (MCB)
ETIM 6.0	EC000042 - Miniature circuit breaker (MCB)

by ABB

Dimensions	
Weight	0.125 kg

Package Information	
Standard packing	12

Operating Performance	
Operating temperature	-25°C / 55°C