



Representative Image

Ref. No. 690300 | Cat. No. EP103ULH2C03
Description: MCB Miniature circuit breaker ElfaPlus EP100 ULH 3P 3A C GE
EAN 5413656903000
Home > Modular DIN-rail devices > Circuit Protection > MCB DIN-rail

- **Safe and reliable**
 - Clear print
 - High degree of insulation IP20
 - Padlocking toggle
 - Sealed terminals
 - **User friendly**
 - **Multifunctional**
 - Motor operator : same device left and right assembly
 - Common device for all products
 - Shunt trip and under voltage relay
 - Auxiliaries
 - **Easy to install**
 - >Different connection techniques
 - High torque performance 4.5 Nm
 - High capacity terminals 35mm²

Descriptors

Category	MCB DIN-rail
Family	Circuit protection

Specifications

In (A)	3
Number of poles	3P
Number of modules	3
Curve Type	C (5-10 In)
Group	ElfaPlus
Range	Commercial - Industrial
Switch	EP100 ULH : 10kA - UL Listed 489
Connections- Top	Screw
Connections- Bottom	Screw
Standards	10kA domestic BS EN 60898 10kA UL498 15-40kA industrial BS EN 60947-2
AC/DC	AC
Logo	GE
Rated voltage	120 V / 240 V
Short-circuit capacity (kA)	10
Selectivity class	3
Terminal capacity max (mm ²)	25-35 mm ²
Electrical service life	20000/10000
Minimum operating voltage U _{bmin} (V)	12 V
Terminal capacity min (mm ²)	0.75 / 1 mm ²
Tropicalisation	95%RH at 55°C

Classifications

Approvals	CCC CE CEBEC EAC UL
ETIM 5.0	EC000042 - Miniature circuit breaker (MCB)
ETIM 6.0	EC000042 - Miniature circuit breaker (MCB)

Dimensions

Weight	0.390 kg
--------	----------

Package Information

Standard packing	4
------------------	---

Operating Performance

Operating temperature	-25°C / 55°C
-----------------------	--------------