

Representative Image

Catalog No. A12A-G

Description: PVC CTD CHANNEL STRUT 10FT GRY

UPC No 704508438425

Home > Cable Protection Systems > Ocal > Steel channels

PVC Coated Back to Back Channel Strut, 1-5/8 Inch Depth, 12 Gauge, 10 Foot Long, Steel, Gray

Descriptors

Category	Steel channels
Special Features	Channels Cold Formed from Hot-Rolled Pickled and Oiled Strip Steel

Specifications

Gauge	12
Finish	PVC Coated
Color	Gray

Classifications

Brand Name	Ocal

Dimensions

Length	10 ft
Depth	1-5/8 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000386 Support/profile rail
Length	3048 mm
Width	41.28 mm
Height	82.55 mm
Profile shape	U-profile
Model	Double profile
Material	Steel

by ABB

ETIM	EC000386 Support/profile rail
Surface protection	Other
Colour	Stone grey