



Representative Image

Catalog No. C14HS-G

Description: PVC CTD 1/2SLOT CHNL STRUT 10FT GRY

UPC No 704508358105

Home > Cable Protection Systems > Ocal > Steel channels

PVC Coated Half Slot Combination Channel, 13/16 Inch Depth, 14 Gauge, 10 Foot Long, Steel, Gray

Descriptors

Category	Steel channels
Special Features	Channels Cold Formed from Hot-Rolled Pickled and Oiled Strip Steel

Specifications

Gauge	14
Finish	PVC Coated
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	10 ft
Depth	13/16 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000386 Support/profile rail
Length	3048 mm
Width	41.28 mm
Height	20.64 mm
Profile shape	U-profile
Material	Steel
Surface protection	Other


by ABB

ETIM	EC000386 Support/profile rail
Colour	Stone grey