



Representative Image

Catalog No. 54866BESP

Description: 54866BE SILVER PLATED

UPC No 786209995964

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper Two-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size 4/0 AWG, 1/2 Inch Bolt Size, 1-3/4 Inch Hole Spacing, Silver Plated, Die Code 54, Die Color Code Purple

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	4/0 AWG
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Purple

Classifications

Brand Name	Color Keyed / Blackburn
------------	-------------------------

Dimensions

Stud Size	1/2 in
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper

by ABB

ETIM	EC001051 Tube cable lug for copper conductors
Surface protection	Other
Number of mounting holes	2
AWG size	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	1097195_2015-02-20	N/A