Representative Image

Catalog No. U010010

Description: MW 20A GFCI SURF UNMTRD

UPC No 784567203004

Home > Power Outlets

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Power Outlets

Specifications

Mounting	Surface
Heads	1
Metering	Unmetered
Receptacles	5-20WR2GFCI
Feed	Overhead
AIC	10,000
Amps	20 A
Cabinet Size	5 in. W X 7 in. H
Circuit Protection	None
Hub Provision	Yes
Installed Breaker	None
Load Center	None
Loop Feed	No
Phase	1
Suitable for Service Equipment	No
Unit Weight	4.5 lb
Volts	120

Classifications

Standard Package	1
Stock Class Code	Stock

Approvals

Certification	UL/CUL