



Representative Image

## Catalog No. COND1/2-G

**Description:** PVC CTD COND 1/2IN RGD STL GRAY

**UPC No** 704508261016

**Home > Cable Protection Systems > Ocal > Electrical conduit**

PVC Coated Conduit, Pipe Size 1/2 Inch/16 Metric, Outside Diameter with PVC .92 Inch/23.30 Millimeters, Nominal Wall Thickness with PVC .14 Inch/3.56 Millimeters, Length without Couplings 9 Feet 11-1/4 Inch/3.03 Meters, Hot-dip Galvanized Steel, Gray

### Descriptors

|                  |                                             |
|------------------|---------------------------------------------|
| Category         | Electrical conduit                          |
| Special Features | Color-Coded Thread Protectors               |
| Application      | Corrosion Protection for Electrical Systems |

### Specifications

|          |                    |
|----------|--------------------|
| Material | Steel              |
| Finish   | Hot-Dip Galvanized |
| Color    | Gray               |

### Classifications

|            |                   |
|------------|-------------------|
| Brand Name | Ocal              |
| Standard   | cULus E46453, CSA |

### Dimensions

|                  |                    |
|------------------|--------------------|
| Trade Size       | 1/2 in             |
| Outside Diameter | 0.92 in , 23.30 mm |
| Inside Diameter  | 0.63 in , 16.10 mm |
| Length           | 9.94 ft , 3.03 m   |
| Wall Thickness   | 0.14 in , 3.56 mm  |

### Compliance and Certifications

|       |                             |
|-------|-----------------------------|
| RoHS  | RoHS3 Compliant             |
| REACH | REACH 253 Compliant         |
| TSCA  | TSCA Section 6(h) Compliant |

### ETIM Classification

|                      |                                   |
|----------------------|-----------------------------------|
| ETIM                 | EC001179 Protective metallic hose |
| Nominal size in inch | 1/2 inch                          |

**by ABB**

|                    |                                   |
|--------------------|-----------------------------------|
| ETIM               | EC001179 Protective metallic hose |
| Outer diameter     | 23.3 mm                           |
| Inner diameter     | 21.3 mm                           |
| Material           | Steel                             |
| Surface protection | Other                             |
| Colour             | Grey                              |
| Bending strength   | Rigid                             |

**Certification/Standard**

| CLASS | File Number | Class  | CCN | Certificate Number | Library Number |
|-------|-------------|--------|-----|--------------------|----------------|
| CSA   | 110787      | 184105 | N/A | 2177301            | N/A            |