



Representative Image

Alternate Catalog No. EF370-380 Catalog No. 1SAX611001R1101

Description: EF370-380 Electronic Overload Relay

UPC No 4013614442216

Home > Contactors & Starters > Overload Relays

The EF205-210 is an self-supplied electronic overload relay, which means no extra external supply is needed. It offers reliable and fast protection for motors in the event of overload or phase failure. Easy to use like a thermal overload relay and compatible with standard motor applications, the electronic overload relay is convincing, above all, due to its wide setting range, high accuracy, high operational temperature range and the possibility to select a trip class (10E, 20E, 30E). Further features are the temperature compensation, trip contact (NC), signal contact (NO), automatic- or manual reset selectable, trip-free mechanism, STOP- and Test function and a trip indication. The overload relays are connected directly to the contactors. The EF205 and EF370 have ATEX and IECEx certification 1) 1) ATEX is valid for products produced from week 42, 2014. IECEx is valid for products produced from week 15, 2017.

Descriptors

| | |
|----------|-----------------|
| Category | Overload Relays |
|----------|-----------------|

Specifications

| | |
|---------------------------------------|---|
| Product Name | Electronic Overload Relay |
| Rated Operational Voltage | Auxiliary Circuit 600 V AC / DC Main Circuit 1000 V AC |
| Rated Operational Current | 380 A |
| Setting Range | 115 ... 380 A |
| Rated Impulse Withstand Voltage | Auxiliary Circuit 6 kV Main Circuit 8 kV |
| Rated Insulation Voltage | 1000 V |
| Number of Poles | 3 |
| Number of Auxiliary Contacts NC | 1 |
| Number of Auxiliary Contacts NO | 1 |
| Number of Protected Poles | 3 |
| Trip Class | class 10E class 20E class 30E |
| Conventional Free-air Thermal Current | Auxiliary Circuit NC 5 A Auxiliary Circuit NO 5 A |
| Rated Frequency | Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Main Circuit 50Hz Main Circuit 60 Hz |
| Rated Operational Current AC-3 | 380 A |
| Degree of Protection | Housing IP20 Main Circuit Terminals IP00 |
| Pollution Degree | 3 |
| Suitable For | A210 A260 A300 AF210 AF260 AF300 AF265 AF305 AF370 |


by ABB

Specifications

| | |
|--|--|
| Rated Operational Current AC-15 | (240 V) NC 3 A (240 V) NO 3 A (400 V) NC 1.1 A (400 V) NO 1.1 A (500 V) NC 0.75 A (500 V) NO 0.75 A |
| Rated Operational Current DC-13 | (125 V) NC 0.55 A (125 V) NO 0.5 A (24 V) NC 1.5 A (24 V) NO 1.5 A (250 V) NC 0.27 A (250 V) NO 0.27 A (60 V) NC 0.55 A (60 V) NO 0.55 A |
| Connecting Capacity Main Circuit | Hole Diameter > 10 mm ² Rigid or Flexible with Cable Lug 1x 50 ... 240 mm ² Rigid or Flexible with Cable Lug 2x 50 ... 150 mm ² |
| Connecting Capacity Auxiliary Circuit | Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ² |
| Wire Stripping Length | Auxiliary Circuit 9 mm |
| Tightening Torque | Auxiliary Circuit 0.8 ... 1.2 N·m Main Circuit 28 N·m |
| Mounting Position | Position 1 to 6 |
| Power Loss | at Rated Operating Conditions per Pole 0.37 ... 4.043 W |
| Standards | IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 |
| Recommended Screw Driver | Auxiliary Circuit Pozidriv 2 |
| Maximum Operating Voltage UL/CSA | Main Circuit 600 V AC |
| Ampere Rating UL/CSA | 380 A |
| Contact Rating UL/CSA | (NC:) B600 (NC:) Q600 (NO:) B600 (NO:) Q600 |
| Connecting Capacity Main Circuit UL/CSA | Stranded 1/2 x 1-500 AWG |
| Ambient Air Temperature | Operation -25 ... +70 °C Operation Compensated -25 ... +70 °C Storage -50 ... +85 °C |
| Ambient Air Temperature Compensation | Yes |
| Connecting Capacity Auxiliary Circuit UL/CSA | Flexible 1/2x 18-10 AWG Stranded 1/2x 18-10 AWG |
| Resistance to Shock acc. to IEC 60068-2-27 | 11 ms Pulse 25g |
| Maximum Operating Altitude Permissible | 2000 m |
| RoHS Status | Following EU Directive 2011/65/EU |
| Resistance to Vibrations acc. to IEC 60068-2-6 | 5g / 3 ... 150 Hz |
| Tightening Torque UL/CSA | Auxiliary Circuit 7 ... 11 in·lb Main Circuit 247 in·lb |
| Object Classification Code | F |

Classifications

| | |
|----------|--------------------------------------|
| ETIM 5.0 | EC001080 - Electronic overload relay |
| ETIM 6.0 | EC001080 - Electronic overload relay |
| ETIM 7 | EC001080 - Electronic overload relay |
| eClass | 7.0 27371502 |
| ETIM 4 | EC001080 - Electronic overload relay |

Dimensions

| | |
|----------------------------|----------|
| Product Net Width | 105 mm |
| Product Net Height | 187.6 mm |
| Product Net Weight | 1.338 kg |
| Product Net Depth / Length | 122.8 mm |

Package Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 195 mm |
| Package Level 1 Depth / Length | 140 mm |
| Package Level 1 Gross Weight | 1.706 kg |
| Package Level 1 EAN | 4013614442216 |
| Package Level 1 Height | 199 mm |

Ordering

| | |
|-----------------------|--|
| ECN | N |
| Customs Tariff Number | 85364900 |
| ECCN | N |
| ABB MDF Code | 3DL - Relays (LV / Control + Protection) |