



Representative Image

Alternate Catalog No. EF750 Catalog No. 1SAX821001R1101

Description: EF750-800 Electronic Overload Relay

UPC No 4013614487422

Home > Contactors & Starters > Overload Relays

The EF460-500 is an self-supplied electronic overload relay, which means no extra external supply is needed. It offers reliable and fast protection for motors in the event of overload or phase failure. Easy to use like a thermal overload relay and compatible with standard motor applications, the electronic overload relay is convincing, above all, due to its wide setting range, high accuracy, high operational temperature range and the possibility to select a trip class (10E, 20E, 30E). Further features are the temperature compensation, trip contact (NC), signal contact (NO), automatic- or manual reset selectable, trip-free mechanism, STOP- and Test function and a trip indication. The overload relays are connected directly to the contactors. The EF460 and EF750 have ATEX and IECEx certification 1) 1) ATEX is valid for products produced from week 42, 2014. IECEx is valid for products produced from week 15, 2017.

Descriptors

Category	Overload Relays
----------	-----------------

Specifications

Product Name	Electronic Overload Relay
Rated Operational Voltage	Auxiliary Circuit 600 V AC / DC Main Circuit 1000 V AC
Rated Operational Current	800 A
Setting Range	250 ... 800 A
Rated Impulse Withstand Voltage	Auxiliary Circuit 6 kV Main Circuit 8 kV
Rated Insulation Voltage	1000 V
Number of Poles	3
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Number of Protected Poles	3
Trip Class	class 10E class 20E class 30E
Conventional Free-air Thermal Current	Auxiliary Circuit NC 6 A Auxiliary Circuit NO 6 A
Rated Frequency	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Main Circuit 50Hz Main Circuit 60 Hz
Rated Operational Current AC-3	800 A
Degree of Protection	Housing IP20 Main Circuit Terminals IP00
Pollution Degree	3
Suitable For	AF580 AF750
Rated Operational Current AC-15	(240 V) NC 3 A (240 V) NO 3 A (400 V) NC 1.1 A (400 V) NO 1.1 A (500 V) NC 0.75 A (500 V) NO 0.75 A

Specifications

Rated Operational Current DC-13	(125 V) NC 0.55 A (125 V) NO 0.5 A (24 V) NC 1.5 A (24 V) NO 1.5 A (250 V) NC 0.27 A (250 V) NO 0.27 A (60 V) NC 0.55 A (60 V) NO 0.55 A
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Wire Stripping Length	Auxiliary Circuit 9 mm
Tightening Torque	Auxiliary Circuit 0.8 ... 1.2 N·m
Mounting Position	Position 1 to 6
Power Loss	at Rated Operating Conditions per Pole 0 W
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1
Recommended Screw Driver	Auxiliary Circuit Pozidriv 2
Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Ampere Rating UL/CSA	800 A
Contact Rating UL/CSA	(NC:) B600 (NC:) Q600 (NO:) B600 (NO:) Q600
Ambient Air Temperature	Operation -25 ... +70 °C Operation Compensated -25 ... +70 °C Storage -25 ... +70 °C
Ambient Air Temperature Compensation	Yes
Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 18-10 AWG Stranded 1/2x 18-10 AWG
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 25g
Maximum Operating Altitude Permissible	2000 m
RoHS Status	Following EU Directive 2011/65/EU
Resistance to Vibrations acc. to IEC 60068-2-6	3g / 3 ... 150 Hz
Tightening Torque UL/CSA	Auxiliary Circuit 7 ... 1 in·lb
Object Classification Code	F

Classifications

ETIM 5.0	EC001080 - Electronic overload relay
ETIM 6.0	EC001080 - Electronic overload relay
ETIM 7	EC001080 - Electronic overload relay
eClass	7.0 27371502
ETIM 4	EC001080 - Electronic overload relay

Dimensions

Product Net Width	244 mm
Product Net Height	111.6 mm
Product Net Weight	2.765 kg
Product Net Depth / Length	187.73 mm

Package Information

Package Level 1 Units	1 piece
Package Level 1 Width	144 mm
Package Level 1 Depth / Length	270 mm
Package Level 1 Gross Weight	2.915 kg
Package Level 1 EAN	4013614487422
Package Level 1 Height	250 mm

Ordering

ECN	N
Customs Tariff Number	85364900
ECCN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)