

Representative Image

Alternate Catalog No. NFZ40E-21
Catalog No. 1SBH136001R2140

Description: NFZ40E-21 24-60V50/60HZ 20-60VDC Contactor Relay

UPC No 3471523101616

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

NFZ contactor relays are used for switching auxiliary and control circuits. NFZ contactor relays include an electronic coil interface accepting a wide control voltage Uc min. ... Uc max. Only four coils cover control voltages between 24...250 V 50/60 Hz or 12...250 V DC. NF contactor relays can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change NFZ contactor relays allow direct control by PLC-output ≥ 24 V DC 500 mA and obtain a reduced holding coil consumption. NFZ contactor relays withstand short voltage dips and voltage sags (SEMI F47-0706 compliance) between 24...250 V 50/60 Hz NFZ contactor relays have built-in surge protection and do not require additional surge suppressors - Poles: 4-pole contactor relays - Control Circuit: AC or DC operated - Accessories: a wide range of Accessories is available.

Descriptors

Category	AF Contactors
Block Contactor Type	Contactor Relay

Specifications

Product Type	AF
Object Classification Code	K
Terminal Type	Screw Terminals
Rated Control Circuit Voltage	50 Hz /60 Hz 24 ... 60 V DC Operation 20 ... 60 V
Resistance to Vibrations acc. to IEC 60068-2-6	5 ... 300 Hz 4 g closed position / 2 g open position
Number of Auxiliary Contacts NO	4
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Close to Contactor for Storage °C Near Contactor for Operation in Free Air °C
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Number of Auxiliary Contacts NC	0
Tightening Torque UL/CSA	Auxiliary Circuit 11 IA Control Circuit 11 IA
Maximum Operating Altitude Permissible	3000 m
Standards	IEC 60947-5-1 and EN 60947-5-1, UL 508, CSA C22.2 N°14
Conventional Free-air Thermal Current	acc. to IEC 60947-5-1, q = 40 °C 16 A
Rated Operational Current AC-15	(220 / 240 V) 4 A (24 / 127 V) 6 A (500 V) 2 A (690 V) 2 A (400 / 440 V) 3 A
Rated Frequency	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz
Rated Short-time Withstand Current	for 0.1 s A for 1 s A
Maximum Electrical Switching Frequency	AC-15 1200 cycles per hour DC-13 900 cycles per hour
Rated Insulation Voltage	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Maximum Mechanical Switching Frequency	6000 cycles per hour

by ABB

Specifications

Operate Time	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
Secondary Rated Impulse Withstand Voltage	6 kV
Rated Operational Current DC-13	(125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W
Connecting Capacity Control Circuit	Flexible with Ferrule Flexible with Insulated Ferrule Rigid
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m² Flexible with Insulated Ferrule 1x 0.75 ... 2.5/2x 0.75 ... 1.5 m² Rigid 1/2x 1 ... 2.5 m²
Wire Stripping Length	Auxiliary Circuit 10 mm Control Circuit 10 mm

Classifications

ETIM 4	EC000196 - Contactor relay
ETIM 6.0	EC000196 - Contactor relay
ETIM 7	EC000196 - Contactor relay
ETIM 5.0	EC000196 - Contactor relay

Dimensions

Product Net Weight	0.31kg
Product Net Depth / Length	77 mm
Product Net Width	45 mm
Product Net Height	86 mm

Package Information

Package Level 1 Width	87 mm
Package Level 1 Depth / Length	79 mm
Package Level 1 EAN	3471523101616
Package Level 1 Units	box 1 piece
Package Level 2 Height	315 mm
Package Level 2 Units	27 piece
Package Level 3 Units	1296 piece
Package Level 2 Depth / Length	300 mm
Package Level 2 Gross Weight	16.74 kg

Ordering

Minimum Order Quantity	1