



Representative Image

## Alternate Catalog No. NF62E-13 Catalog No. 1SBH137001R1362

**Description:** NF62E-13 100-250V50/60HZ-DC Contactor Relay

**UPC No** 3471523100534

**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

NF contactor relays are used for switching auxiliary and control circuits. NF contactor relays include an electronic coil interface accepting a wide control voltage  $U_c \text{ min.} \dots U_c \text{ max.}$  Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. NF contactor relays can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. NF contactor relays have built-in surge protection and do not require additional surge suppressors. - Poles: 8-pole contactor relays with a non-removable front-mounted auxiliary contact block (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1 and including the "Mechanically Linked" symbol on the contactor relay side) - Control Circuit: AC or DC operated - Accessories: a wide range of Accessories is available.

### Descriptors

Category	AF Contactors
Block Contactor Type	Contactor Relay

### Specifications

Product Type	AF
Object Classification Code	K
Terminal Type	Screw Terminals
Rated Control Circuit Voltage	50 Hz /60 Hz DC Operation 100 ... 250 V
Resistance to Vibrations acc. to IEC 60068-2-6	5 ... 300 Hz 4 g closed position / 2 g open position
Number of Auxiliary Contacts NO	6
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Close to Contactor for Storage °C Near Contactor for Operation in Free Air °C
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Number of Auxiliary Contacts NC	2
Tightening Torque UL/CSA	Auxiliary Circuit 11 IA Control Circuit 11 IA
Maximum Operating Altitude Permissible	3000 m
Standards	IEC 60947-5-1 and EN 60947-5-1, UL 508, CSA C22.2 N°14
Conventional Free-air Thermal Current	acc. to IEC 60947-5-1, $q = 40 \text{ °C}$ 16 A
Rated Operational Current AC-15	(220 / 240 V) 4 A (24 / 127 V) 6 A (500 V) 2 A (690 V) 2 A (400 / 440 V) 3 A
Rated Frequency	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz
Rated Short-time Withstand Current	for 0.1 s A for 1 s A
Maximum Electrical Switching Frequency	AC-15 1200 cycles per hour DC-13 900 cycles per hour
Rated Insulation Voltage	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Maximum Mechanical Switching Frequency	6000 cycles per hour

## Specifications

Operate Time	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
Secondary Rated Impulse Withstand Voltage	6 kV
Rated Operational Current DC-13	(125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W
Connecting Capacity Control Circuit	Flexible with Ferrule Flexible with Insulated Ferrule Rigid
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m <sup>2</sup> Flexible with Insulated Ferrule 1x 0.75 ... 2.5/2x 0.75 ... 1.5 m <sup>2</sup> Rigid 1/2x 1 ... 2.5 m <sup>2</sup>
Wire Stripping Length	Auxiliary Circuit 10 mm Control Circuit 10 mm

## Classifications

ETIM 4	EC000196 - Contactor relay
ETIM 6.0	EC000196 - Contactor relay
ETIM 7	EC000196 - Contactor relay
ETIM 5.0	EC000196 - Contactor relay

## Dimensions

Product Net Weight	0.32kg
Product Net Depth / Length	110.5 mm
Product Net Width	45 mm
Product Net Height	86 mm

## Package Information

Package Level 1 Width	87 mm
Package Level 1 Depth / Length	113 mm
Package Level 1 EAN	3471523100534
Package Level 1 Units	box 1 piece
Package Level 2 Height	315 mm
Package Level 2 Units	18 piece
Package Level 3 Units	864 piece
Package Level 2 Depth / Length	300 mm
Package Level 2 Gross Weight	11.52 kg

## Ordering

Minimum Order Quantity	1
------------------------	---