



Representative Image

Alternate Catalog No. AF16Z-30-01K-23 Catalog No. 1SBL176005R2301

Description: AF16Z-30-01K-23 100-250V50/60HZ-DC Contactor

UPC No 3471523156234

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF16Z..K 3-pole contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF..Z contactors include an electronic coil interface accepting a wide control voltage U_c min. ... U_c max. Only four coils cover control voltages between 24...250 V 50/60 Hz or 12...250 V DC. AF..Z contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF..Z contactors allow direct control by PLC-output ≥ 24 V DC 500 mA and obtain a reduced holding coil consumption. AF..Z contactors withstand short voltage dips and voltage sags (SEMI F47-0706 compliance) between 24...250 V 50/60 Hz. AF..Z contactors have built-in surge protection and do not require additional surge suppressors. AF16Z..K include Push-in Spring terminals. Only one push is all you need for extremely fast wiring: faster than ever installation, easier than ever wiring, reliable as ever connections. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks. (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Accessories: a wide range of accessories is available.

Descriptors

| | |
|----------------------|------------------|
| Category | AF Contactors |
| Block Contactor Type | 3-Pole Contactor |

Specifications

| | |
|--|---|
| Product Type | AF |
| General Use Rating UL/CSA | (600 V AC) 30 A |
| Object Classification Code | Q |
| Terminal Type | Push-in Spring Terminals |
| Rated Control Circuit Voltage | 50 Hz /60 Hz DC Operation 100 ... 250 V |
| Number of Main Contacts NO | 3 |
| Number of Main Contacts NC | 0 |
| Climatic Withstand | Category B according to IEC 60947-1 Annex Q |
| Resistance to Vibrations acc. to IEC 60068-2-6 | 5 ... 300 Hz 4 g closed position / 2 g open position |
| Number of Auxiliary Contacts NO | 0 |
| RoHS Status | Following EU Directive 2011/65/EU |
| Reference Ambient Air Temperature | Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C |
| Rated Operational Voltage | Auxiliary Circuit 690 V Main Circuit 690 V |
| Number of Auxiliary Contacts NC | 1 |
| Maximum Operating Altitude Permissible | 3000 m |
| Rated Operational Current AC-1 | (690 V) 40 °C 30 A (690 V) 60 °C 30 A (690 V) 70 °C 26 A |
| Rated Operational Power AC-3 | (220 / 230 / 240 V) 4 KWT (380 / 400 V) 7.5 KWT (415 V) 9 KWT (440 V) 9 KWT (500 V) 9 KWT (690 V) 9 KWT |

Specifications

| | |
|---|---|
| Horsepower Rating UL/CSA | (220 ... 240 V AC) Three Phase 5 hp (440 ... 480 V AC) Three Phase 10 hp (550 ... 600 V AC) Three Phase 15 hp (120 V AC) Single Phase 1-1/2 hp (200 ... 208 V AC) Three Phase 5 hp (240 V AC) Single Phase 3 hp |
| Conventional Free-air Thermal Current | acc. to IEC 60947-5-1, $q = 40\text{ °C}$ 16 A acc. to IEC 60947-4-1, Open Contactors $q = 40\text{ °C}$ 35 A |
| Rated Operational Current AC-15 | (220 / 240 V) 4 A (24 / 127 V) 6 A (500 V) 2 A (690 V) 2 A (400 / 440 V) 3 A |
| Rated Frequency | Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Main Circuit 50Hz Main Circuit 60 Hz |
| Rated Short-time Withstand Current | at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 35 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 60 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 80 A for 0.1 s 140 A for 1 s 100 A |
| Rated Operational Current AC-3 | (220 / 230 / 240 V) 60 °C 18 A (380 / 400 V) 60 °C 18 A (415 V) 60 °C 18 A (440 V) 60 °C 18 A (500 V) 60 °C 15 A (690 V) 60 °C 10.5 A |
| Maximum Electrical Switching Frequency | AC-1 600 cycles per hour AC-2 / AC-4 300 cycles per hour AC-3 1200 cycles per hour AC-15 1200 cycles per hour DC-13 900 cycles per hour |
| Rated Insulation Voltage | acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V |
| Maximum Breaking Capacity | $\cos\phi=0.45$ ($\cos\phi=0.35$ for $I_e > 100\text{ A}$) at 440 V 250 A $\cos\phi=0.45$ ($\cos\phi=0.35$ for $I_e > 100\text{ A}$) at 690 V 106 A |
| Maximum Mechanical Switching Frequency | 3600 cycles per hour |
| Operate Time | Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms |
| Secondary Rated Impulse Withstand Voltage | 6 kV |
| Connecting Capacity Main Circuit | Flexible 1/2x 0.5 ... 4 m ² Rigid 1/2x 1 ... 6 m ² Flexible with Ferrule 1/2x 0.5 ... 4 m ² Flexible with Insulated Ferrule 1x 0.5 ... 4 m ² /2x 0.5 ... 2.5 m ² / |
| Rated Operational Current DC-13 | (125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W |
| Connecting Capacity Control Circuit | Flexible with Ferrule 1/2x 0.5 ... 2.5 m ² Flexible with Insulated Ferrule 1/2x 0.5 ... 1.5 m ² Rigid 1/2x 1 ... 2.5 m ² Flexible 1/2x 0.5 ... 2.5 m ² |
| Degree of Protection | acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Connecting Capacity Auxiliary Circuit | Flexible with Ferrule 1/2x 0.5 ... 2.5 m ² Flexible with Insulated Ferrule 1/2x 0.5 ... 1.5 m ² Flexible 1/2x 0.5 ... 2.5 m ² Rigid 1/2x 1 ... 2.5 m ² |
| Screw Terminal Type | Push-in Spring Terminals |

Specifications

| | |
|-----------------------|--|
| Wire Stripping Length | Auxiliary Circuit 10 mm Control Circuit 10 mm Main Circuit 12 mm |
|-----------------------|--|

Classifications

| | |
|----------|---|
| ETIM 4 | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching |
| ETIM 7 | EC000066 - Power contactor, AC switching |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |

Dimensions

| | |
|----------------------------|---------|
| Product Net Weight | 0.315kg |
| Product Net Depth / Length | 77 mm |
| Product Net Width | 45 mm |
| Product Net Height | 92.3 mm |

Package Information

| | |
|--------------------------------|---------------|
| Package Level 1 Width | 93 mm |
| Package Level 1 Height | 45 mm |
| Package Level 1 Depth / Length | 86 mm |
| Package Level 1 EAN | 3471523156234 |
| Package Level 1 Units | box 1 piece |
| Package Level 2 Width | 250 mm |
| Package Level 2 Height | 315 mm |
| Package Level 1 Gross Weight | 0.33 kg |
| Package Level 2 Units | box 21 piece |
| Package Level 3 Units | 1080 piece |
| Package Level 2 Depth / Length | 300 mm |
| Package Level 2 Gross Weight | 14.85 kg |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 |
| Customs Tariff Number | 85364900 |