

Representative Image

Alternate Catalog No. AF26ZB-30-00RT-22
Catalog No. 1SBL236060R2200

Description: AF26ZB-30-00RT-22 48-130V50/60HZ-DC Contactor

UPC No 3471523128521

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF26ZB..RT 3-pole contactors comply with the latest railway rolling stock standards and allow installation in passengers or driver cabins for trains frequently operating tunnels or undergrounds. They are mainly used for controlling 3-phase motors and power circuits up to 690 V AC and 220 V DC. Improve the compactness of the installations thanks to reduced dimension and side-by-side mounting requiring less 15% width (without spacing) from -40 °C up to +70 °C. Meet all main rollling stocks standards: IEC 60947-4-1, IEC 60947-5-1, IEC 60077-1/-2 and applicable parts of EN 50155 standards, shocks and vibration withstand conforming to IEC 61373 cat. 1, class B. Reach the highest levels in fire and smoke behaviour with compliance to European standard EN 45545-2 (HL2, HL3 hazard levels) in group mounting Reduce train energy with lighter devices and requiring 68% less coil energy consumption in operation. Electronic coil interface handling large DC voltage fluctuation voltage, including several Uc DC control voltages used for battery supply and accepting sinusoïdal AC 50/60 Hz control supplies included inside Ucmin.... Ucmax voltage range. Max permitted AC 50/60 Hz control voltage must not be exceeded (see technical data). Wide range of auxiliary contact blocks for front and side mounting.

Descriptors

Category	AF Contactors
Block Contactor Type	3-Pole Contactor

Specifications

Product Type	AF
General Use Rating UL/CSA	(600 V AC) 45 A
Object Classification Code	Q
Terminal Type	Ring-Tongue Terminals
Rated Control Circuit Voltage	50 Hz /60 Hz DC Operation 48 ... 130 V
Number of Main Contacts NO	3
Number of Main Contacts NC	0
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Number of Auxiliary Contacts NO	0
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C
Rated Operational Voltage	Main Circuit 690 V
Number of Auxiliary Contacts NC	0
Maximum Operating Altitude Permissible	3000 m
Rated Operational Current AC-1	(690 V) 40 °C 45 A (690 V) 60 °C 40 A (690 V) 70 °C 32 A
Rated Operational Power AC-3	(220 / 230 / 240 V) 6.5 KWT (380 / 400 V) 11 KWT (415 V) 11 KWT (440 V) 15 KWT (500 V) 15 KWT (690 V) 15 KWT

by ABB

Specifications

Horsepower Rating UL/CSA	(220 ... 240 V AC) Three Phase 7-1/2 hp (440 ... 480 V AC) Three Phase 15 hp (550 ... 600 V AC) Three Phase 20 hp (120 V AC) Single Phase 2 hp (200 ... 208 V AC) Three Phase 7-1/2 hp (240 V AC) Single Phase 3 hp
Conventional Free-air Thermal Current	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 50 A
Rated Frequency	Main Circuit 50Hz Main Circuit 60 Hz
Rated Short-time Withstand Current	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 350 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 50 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 700 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A for 1 s - A
Rated Operational Current AC-3	(220 / 230 / 240 V) 60 °C 26 A (380 / 400 V) 60 °C 26 A (415 V) 60 °C 26 A (440 V) 60 °C 26 A (500 V) 60 °C 23 A (690 V) 60 °C 17 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 1200 cycles per hour
Rated Insulation Voltage	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for Ie > 100 A) at 440 V 500 A cos phi=0.45 (cos phi=0.35 for Ie > 100 A) at 690 V 200 A
Maximum Mechanical Switching Frequency	3600 cycles per hour
Operate Time	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
Secondary Rated Impulse Withstand Voltage	6 kV
Screw Terminal Type	Ring-Tongue Terminals

Classifications

ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 5.0	EC000066 - Magnet contactor, AC-switching

Dimensions

Product Net Weight	0.36 kg
Product Net Depth / Length	86 mm
Product Net Width	45 mm
Product Net Height	86 mm

Package Information

Package Level 1 Width	87 mm
Package Level 1 Height	47 mm
Package Level 1 Depth / Length	87 mm
Package Level 1 EAN	3471523128521
Package Level 1 Units	box 1 piece
Package Level 2 Width	250 mm
Package Level 2 Height	315 mm

Package Information

Package Level 1 Gross Weight	0.36 kg
Package Level 2 Units	21 piece
Package Level 3 Units	1080 piece
Package Level 2 Depth / Length	300 mm
Package Level 2 Gross Weight	16.2 kg

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85364900