



Representative Image

## Alternate Catalog No. AF38-30-00K-12 Catalog No. 1SBL297005R1200

**Description: AF38-30-00K-12 48-130V50/60HZ-DC Contactor**

**UPC No 3471523155329**

**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

AF38..K 3-pole contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF... contactors include an electronic coil interface accepting a wide control voltage  $U_c$  min. ...  $U_c$  max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. AF38..K include Push-in Spring terminals. Only one push is all you need for extremely fast wiring: faster than ever installation, easier than ever wiring, reliable as ever connections. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, front and side-mounted add-on auxiliary contact blocks. (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Accessories: a wide range of accessories is available.

### Descriptors

|                      |                  |
|----------------------|------------------|
| Category             | AF Contactors    |
| Block Contactor Type | 3-Pole Contactor |

### Specifications

|  |   |
|--|---|
| Product Type                                   | AF  |
| General Use Rating UL/CSA                      | (600 V AC) 45 A   |
| Object Classification Code                     | Q   |
| Terminal Type                                  | Push-in Spring Terminals  |
| Rated Control Circuit Voltage                  | 50 Hz /60 Hz DC Operation 48 ... 130 V  |
| Number of Main Contacts NO                     | 3   |
| Number of Main Contacts NC                     | 0   |
| Climatic Withstand                             | Category B according to IEC 60947-1 Annex Q   |
| Resistance to Vibrations acc. to IEC 60068-2-6 | 5 ... 300 Hz 4 g closed position / 2 g open position  |
| Number of Auxiliary Contacts NO                | 0   |
| RoHS Status                                    | Following EU Directive 2011/65/EU   |
| Reference Ambient Air Temperature              | Close to Contactor for Storage -60 ... +80 °C<br>Close to Contactor without Thermal O/L Relay -40 ... +70 °C<br>Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C |
| Rated Operational Voltage                      | Main Circuit 690 V  |
| Number of Auxiliary Contacts NC                | 0   |
| Maximum Operating Altitude Permissible         | 3000 m  |
| Rated Operational Current AC-1                 | (690 V) 40 °C 50 A<br>(690 V) 60 °C 42 A<br>(690 V) 70 °C 37 A<br>(220 / 230 / 240 V) 11 KWT<br>(380 / 400 V) 18.5 KWT<br>(415 V) 18.5 KWT                                      |
| Rated Operational Power AC-3                   | (440 V) 22 KWT<br>(500 V) 22 KWT<br>(690 V) 22 KWT  |

## Specifications

|   |  |
|---|--|
| Horsepower Rating UL/CSA                  | (220 ... 240 V AC) Three Phase 10 hp<br>(440 ... 480 V AC) Three Phase 25 hp<br>(550 ... 600 V AC) Three Phase 30 hp<br>(120 V AC) Single Phase 2 hp<br>(200 ... 208 V AC) Three Phase 10 hp<br>(240 V AC) Single Phase 5 hp   |
| Conventional Free-air Thermal Current     | acc. to IEC 60947-4-1, Open Contactors $q = 40\text{ }^{\circ}\text{C}$ 50 A   |
| Rated Frequency                           | Main Circuit 50Hz<br>Main Circuit 60 Hz  |
| Rated Short-time Withstand Current        | at $40\text{ }^{\circ}\text{C}$ Ambient Temp, in Free Air, from a Cold State 10 s 350 A<br>at $40\text{ }^{\circ}\text{C}$ Ambient Temp, in Free Air, from a Cold State 15 min 50 A<br>at $40\text{ }^{\circ}\text{C}$ Ambient Temp, in Free Air, from a Cold State 1 min 150 A<br>at $40\text{ }^{\circ}\text{C}$ Ambient Temp, in Free Air, from a Cold State 1 s 700 A<br>at $40\text{ }^{\circ}\text{C}$ Ambient Temp, in Free Air, from a Cold State 30 s 225 A for 1 s - A |
| Rated Operational Current AC-3            | (220 / 230 / 240 V) $60\text{ }^{\circ}\text{C}$ 40 A<br>(380 / 400 V) $60\text{ }^{\circ}\text{C}$ 38 A<br>(415 V) $60\text{ }^{\circ}\text{C}$ 38 A<br>(440 V) $60\text{ }^{\circ}\text{C}$ 38 A<br>(500 V) $60\text{ }^{\circ}\text{C}$ 33 A<br>(690 V) $60\text{ }^{\circ}\text{C}$ 24 A   |
| Maximum Electrical Switching Frequency    | AC-1 600 cycles per hour<br>AC-2 / AC-4 150 cycles per hour<br>AC-3 1200 cycles per hour   |
| Rated Insulation Voltage                  | acc. to UL/CSA 600 V<br>acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V   |
| Maximum Breaking Capacity                 | $\cos\phi=0.45$ ( $\cos\phi=0.35$ for $I_e > 100\text{ A}$ ) at 440 V 500 A<br>$\cos\phi=0.45$ ( $\cos\phi=0.35$ for $I_e > 100\text{ A}$ ) at 690 V 200 A   |
| Maximum Mechanical Switching Frequency    | 3600 cycles per hour   |
| Operate Time                              | Between Coil De-energization and NC Contact Closing 13 ... 98 ms<br>Between Coil De-energization and NO Contact Opening 11 ... 95 ms<br>Between Coil Energization and NC Contact Opening 38 ... 90 ms<br>Between Coil Energization and NO Contact Closing 40 ... 95 ms   |
| Secondary Rated Impulse Withstand Voltage | 6 kV   |
| Connecting Capacity Main Circuit          | Flexible 1/2x 1 ... 6 m <sup>2</sup><br>Rigid 1/2x 1 ... 10 m <sup>2</sup><br>Flexible with Ferrule 1/2x 1 ... 6 m <sup>2</sup><br>Flexible with Insulated Ferrule 1/2x 1 ... 6 m <sup>2</sup>   |
| Connecting Capacity Control Circuit       | Flexible with Ferrule 1/2x 0.5 ... 2.5 m <sup>2</sup><br>Flexible with Insulated Ferrule 1/2x 0.5 ... 1.5 m <sup>2</sup><br>Flexible 1/2x 0.5 ... 2.5 m <sup>2</sup><br>Rigid 1/2x 1 ... 2.5 m <sup>2</sup>  |
| Degree of Protection                      | acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20<br>acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20   |
| Screw Terminal Type                       | Push-in Spring Terminals   |
| Wire Stripping Length                     | Control Circuit 10 mm<br>Main Circuit 14 mm  |

## Classifications

|          |   |
|----------|---|
| ETIM 4   | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching  |
| ETIM 7   | EC000066 - Power contactor, AC switching  |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |

## Dimensions

|                            |         |
|----------------------------|---------|
| Product Net Weight         | 0.33kg  |
| Product Net Depth / Length | 86 mm   |
| Product Net Width          | 45 mm   |
| Product Net Height         | 92.3 mm |

## Package Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Width          | 93 mm         |
| Package Level 1 Height         | 45 mm         |
| Package Level 1 Depth / Length | 86 mm         |
| Package Level 1 EAN            | 3471523155329 |
| Package Level 1 Units          | box 1 piece   |
| Package Level 2 Width          | 250 mm        |
| Package Level 2 Height         | 315 mm        |
| Package Level 1 Gross Weight   | 0.345 kg      |
| Package Level 2 Units          | box 21 piece  |
| Package Level 3 Units          | 1080 piece    |
| Package Level 2 Depth / Length | 300 mm        |
| Package Level 2 Gross Weight   | 15.525 kg     |

## Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 1        |
| Customs Tariff Number  | 85364900 |