

## Alternate Catalog No. PSR30-600-11 Catalog No. 1SFA896109R1100

**Description:** PSR SSTR,600V/24V AC/DC,28A

**UPC No** 7320500477205

**Home > Soft Starters > Softstarter - Open (PSR)**

The softstarter PSR30-600-11 has a rated maximum operational current of 30 A with an operating voltage span from 208...600 V AC. The rated control voltage is 24 V AC/DC. PSR features a two-phase control soft start and stop through a voltage ramp. It has built-in bypass for easy installation and energy saving. A RUN and a TOR signal is available from a relay output in NO (normally open state). The start/stop ramp and time is easy to set by three potentiometers on the front. PSR is often used in combination with a manual motor starter (MMS) from ABB, so mechanical connection kits are available. Another popular option is Fieldbus communication, which can be enabled by an external adaptor and a Fieldbus plug. The PSR range is our most compact softstarters with basic functionality and values. They are suitable for small three-phase motors with nominal currents from 3...105 A and can manage up to 100 starts per hour. Common applications are, for example, pumps, fans, compressors, and conveyors.



### Descriptors

Category	Softstarter - Open (PSR)
----------	--------------------------

### Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	24Vac/dc
Normal Duty: Output Current (A)	28
Normal Duty: Motor Power (HP) at 460V	20
Power Dissipation In Watts	36
Height (Inches)	6.3
Width (Inches)	1.77
Depth (Inches)	5.04

### Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

### Dimensions

Weight (lb)	1.43
Height (mm)	160
Width (mm)	45
Depth (mm)	128
Weight (kg)	0.60

**by ABB**