

Representative Image

Alternate Catalog No. PSR37-600-11
Catalog No. 1SFA896110R1100

Description: PSR SSTR,600V/24V AC/DC,34A

UPC No 7320500477212

Home > Soft Starters > Softstarter - Open (PSR)

The softstarter PSR37-600-11 has a rated maximum operational current of 37 A with an operating voltage span from 208...600 V AC. The rated control voltage is 24 V AC/DC. PSR features a two-phase control soft start and stop through a voltage ramp. It has built-in bypass for easy installation and energy saving. A RUN and a TOR signal is available from a relay output in NO (normally open state). The start/stop ramp and time is easy to set by three potentiometers on the front. PSR is often used in combination with a manual motor starter (MMS) from ABB, so mechanical connection kits are available. Another popular option is Fieldbus communication, which can be enabled by an external adaptor and a Fieldbus plug. The PSR range is our most compact softstarters with basic functionality and values. They are suitable for small three-phase motors with nominal currents from 3...105 A and can manage up to 100 starts per hour. Common applications are, for example, pumps, fans, compressors, and conveyors.

Descriptors

Category	Softstarter - Open (PSR)

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	24Vac/dc
Normat Duty: Output Current (A)	34
Normal Duty: Motor Power (HP) at 460V	25
Power Dissipation In Watts	5.5
Height (Inches)	7.36
Width (Inches)	2.13
Depth (Inches)	6.02

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	2.2
Height (mm)	187
Width (mm)	54
Depth (mm)	153
Weight (kg)	1