



Representative Image

## Catalog No. 1SVR427034R2000

**Description:** CP-E 48/5.0 Power supply In:115/230VAC Out: 48VDC/5A

**UPC No** 4016779669726

**Home > Controls & Protective Relays > Power Supplies**

The CP-E 48/5.0 is a power supply from the CP-E range. The primary switch mode power supply offers a wide range input of 90-132 V AC, 180-264 V AC and 210-375 V DC, rated input voltage is 115 or 230 V AC (auto select). The rated output power is 240 W, rated output current is 5 A at an output voltage of 48 V DC. The output voltage is adjustable within a range of 47 to 56 V DC. The power supply provides an U/I output characteristic. In order to increase capacity, up to 3 units can be connected in parallel.

### Descriptors

|          |                |
|----------|----------------|
| Category | Power Supplies |
|----------|----------------|

### Specifications

|                                    |  |
|------------------------------------|--|
| Product Main Type                  | CP-E   |
| Number of phases                   | 1  |
| Input Voltage                      | 90 ... 132 V AC<br>180 ... 264 V AC<br>210 ... 375 V DC  |
| Output Voltage                     | 48 V DC  |
| Output Current                     | 5 A  |
| Output Power                       | 240 W  |
| Function                           | Switch mode power supply   |
| Rated Input Voltage                | 115 / 230 V AC   |
| Rated Frequency Limits             | 47 ... 63 Hz   |
| Characteristic of Output           | U/I characteristic curve   |
| Rated Output Power                 | 240 W  |
| Rated Output Voltage               | 48 V DC  |
| Rated Output Current               | 5 A  |
| Rated Insulation Voltage           | Input Circuit 3 V<br>Output Circuit 3 V<br>Input Circuit 2 V<br>PE 2 V   |
| Degree of Protection               | Housing<br>Terminals IP20<br>IP20  |
| Pollution Degree                   | 2  |
| Connecting Capacity Input Circuit  | Flexible with Ferrule 0.2 ... 4 mm <sup>2</sup><br>Rigid 0.2 ... 6 mm <sup>2</sup>   |
| Connecting Capacity Output Circuit | Flexible with Ferrule 0.2 ... 4 mm <sup>2</sup><br>Rigid 0.2 ... 6 mm <sup>2</sup>   |
| Tightening Torque                  | Input Circuit 1 N-m<br>Output Circuit 0.62 N-m   |
| Wire Stripping Length              | Input Circuit 8 mm<br>Output Circuit 8 mm  |
| Minimum Mounting Distance          | Electrical Conductive Board, Horizontal 25 mm<br>Electrical Conductive Board, Vertical 25 mm<br>Other Device Same Type, Horizontal 25 mm<br>Other Device Same Type, Vertical 25 mm |
| Mounting Position                  | Position 1   |

## Specifications

|   |   |
|---|---|
| Mounting on DIN Rail                      | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715  |
| Standards                                 | ANSI/ISA-12.12<br>CAN/CSA C22.2 No.107.1<br>CAN/CSA C22.2 No.213<br>CAN/CSA C22.2 No.60950<br>EN 50581<br>IEC/EN 60950-1<br>IEC/EN 61000-6-2<br>IEC/EN 61000-6-3<br>UL508<br>UL 60950 |
| Ambient Air Temperature                   | Operation -40 ... +70 °C<br>Storage -40 ... +85 °C  |
| RoHS Status                               | Following EU Directive 2011/65/EU   |
| Connecting Capacity Input Circuit UL/CSA  | Rigid 24-10 AWG   |
| Connecting Capacity Output Circuit UL/CSA | Rigid 24-10 AWG   |
| Tightening Torque UL/CSA                  | Input Circuit 9 in-lb<br>Output Circuit 5.5 in-lb   |
| Object Classification Code                | T   |

## Classifications

|          |                            |
|----------|----------------------------|
| ETIM 4   | EC002540 - DC-power supply |
| ETIM 5.0 | EC002540 - DC-power supply |
| ETIM 6.0 | EC002540 - DC-power supply |
| ETIM 7   | EC002540 - DC-power supply |

## Dimensions

|                            |          |
|----------------------------|----------|
| Product Net Width          | 83 mm    |
| Product Net Height         | 123.6 mm |
| Product Net Depth / Length | 123.6 mm |
| Product Net Weight         | 1.322 kg |

## Package Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Width          | 162 mm        |
| Package Level 1 Depth / Length | 160 mm        |
| Package Level 1 Height         | 104 mm        |
| Package Level 1 Gross Weight   | 1.438 kg      |
| Package Level 1 EAN            | 4016779669726 |
| Package Level 1 Units          | 1 piece       |

## Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 1        |
| Customs Tariff Number  | 85044090 |
| ECCN                   | N        |
| ECN                    | N        |

## Electromagnetic Compatibility

|  |   |
|--|---|
| Electrostatic Discharge (ESD Immunity) acc. to IEC 61000-4-2 | Level 4 Air Discharge 15 kV<br>Level 4 Contact Discharge 8 kV |
|--|---|

## Electromagnetic Compatibility

|  |  |
|--|--|
| Radiated Electromagnetic Field Immunity acc. to IEC 61000-4-3    | Level 3 10 V/m   |
| Electrical Fast Transient (Burst Immunity) acc. to IEC 61000-4-4 | Level 4 Power Supply Port Signal 4 kV                    |
| Surge Immunity acc. to IEC 61000-4-5                             | Level 3 Line-to-Line 2 kV<br>Level 4 Line-to-Ground 4 kV |
| Conducted Disturbances Immunity acc. to IEC 61000-4-6            | Level 3 10 V   |
| Electromagnetic Compatibility (EMC)                              | Immunity - Class B<br>Emission - Class B                 |