

Alternate Catalog No. S802S-K16 Catalog No. 2CCS862001R0467

Description: MCB S800S 2P K 16A

UPC No 7612271201586

Home > Modular DIN Rail Products > Mini Circuit breakers

The S802S-K16 is a 2-pole High Performance Circuit breaker with K-Characteristic, with cage terminal and a rated current of 16 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S802S-K16 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S802S-K16 more comfortable. Due to the fast arc extinction of S802S-K16 your application will be secured.



Representative Image

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|--|---|
| Interrupting Rating acc. to UL1077 | (240 V AC) 30 kA (480Y / 277 V AC) 14 kA (600Y / 347 V AC) 6 kA |
| Number of Poles | 2 |
| Power Loss | at Rated Operating Conditions per Pole 3.5 W |
| Product Main Type | S800S |
| Rated Current | 16 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (240 / 415 V AC) 50 kA (254 / 440 V AC) 30 kA (400 / 690 V AC) 6 kA (125 V DC) 30 kA |
| Rated Voltage (V) | (240 V AC) (480Y / 277 V AC) (600Y / 347 V AC) |
| Standards | IEC/EN 60947-2 UL 1077 |
| Tripping Characteristic | K |