

## Alternate Catalog No. S803S-C50 Catalog No. 2CCS863001R0504

**Description:** MCB S800S 3P C 50A

**UPC No** 7612271200794

**Home > Modular DIN Rail Products > Mini Circuit breakers**



Representative Image

The S803S-C50 is a 3-pole High Performance Circuit breaker with C-characteristic, with cage terminal and a rated current of 50 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S803S-C50 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S803S-C50 more comfortable. Due to the fast arc extinction of S803S-C50 your application will be secured.

### Descriptors

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

### Specifications

|  |   |
|--|---|
| Interrupting Rating acc. to UL1077             | (240 V AC) 30 kA<br>(480Y / 277 V AC) 14 kA<br>(600Y / 347 V AC) 6 kA                         |
| Number of Poles                                | 3   |
| Power Loss                                     | at Rated Operating Conditions per Pole 4.3 W  |
| Product Main Type                              | S800S   |
| Rated Current                                  | 50 A  |
| Rated Short-Circuit Capacity                   | (230 / 400 V AC) 25 kA  |
| Rated Ultimate Short-Circuit Breaking Capacity | (240 / 415 V AC) 50 kA<br>(254 / 440 V AC) 30 kA<br>(400 / 690 V AC) 6 kA<br>(125 V DC) 30 kA |
| Rated Voltage (V)                              | (240 V AC)<br>(480Y / 277 V AC)<br>(600Y / 347 V AC)  |
| Standards                                      | IEC/EN 60947-2<br>IEC/EN 60898-1<br>UL 1077   |
| Tripping Characteristic                        | C   |