

Alternate Catalog No. S803S-C63 Catalog No. 2CCS863001R0634

Description: MCB S800S 3P C 63A

UPC No 7612271200800

Home > Modular DIN Rail Products > Mini Circuit breakers



Representative Image

The S803S-C63 is a 3-pole High Performance Circuit breaker with C-characteristic, with cage terminal and a rated current of 63 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S803S-C63 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S803S-C63 more comfortable. Due to the fast arc extinction of S803S-C63 your application will be secured.

Descriptors

Category	Mini Circuit breakers
----------	-----------------------

Specifications

Interrupting Rating acc. to UL1077	(240 V AC) 30 kA (480Y / 277 V AC) 14 kA (600Y / 347 V AC) 6 kA
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 6.4 W
Product Main Type	S800S
Rated Current	63 A
Rated Short-Circuit Capacity	(230 / 400 V AC) 25 kA
Rated Ultimate Short-Circuit Breaking Capacity	(240 / 415 V AC) 50 kA (254 / 440 V AC) 30 kA (400 / 690 V AC) 6 kA (125 V DC) 30 kA
Rated Voltage (V)	(240 V AC) (480Y / 277 V AC) (600Y / 347 V AC)
Standards	IEC/EN 60947-2 IEC/EN 60898-1 UL 1077
Tripping Characteristic	C