



Representative Image

## Alternate Catalog No. S801C-C16 Catalog No. 2CCS881001R0164

**Description:** MCB S800C 1P D 16A

**UPC No** 7612271212445

**Home > Modular DIN Rail Products > Mini Circuit breakers**

The S801C-C16 is a 1-pole High Performance Circuit breaker with C-characteristic, with cage terminal and a rated current of 16 A. It is a current limiting device with a maximum breaking capacity of 25kA at 240/415V. It can be used for voltages up to 254/440V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S801C-C16 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S801C-C16 more comfortable. Due to the fast arc extinction of S801C-C16 your application will be secured.

### Descriptors

Category	Mini Circuit breakers
----------	-----------------------

### Specifications

Interrupting Rating acc. to UL1077	(240 V AC) 20 kA (277 V AC) 10 kA (125 V DC) 10 kA
Number of Poles	1
Power Loss	at Rated Operating Conditions per Pole 3.1 W
Product Main Type	S800C
Rated Current	16 A
Rated Short-Circuit Capacity	(230 / 400 V AC) 15 kA
Rated Ultimate Short-Circuit Breaking Capacity	(240 / 415 V AC) 25 kA (254 / 440 V AC) 15 kA (125 V DC) 10 kA
Rated Voltage (V)	(240 V AC) (277 V AC) (125 V DC)
Standards	IEC/EN 60947-2 IEC/EN 60898-1 UL 1077
Tripping Characteristic	C