

Alternate Catalog No. S802C-K16 Catalog No. 2CCS882001R0467

Description: S802C K16 HIGH PERFORMANCE MCB

UPC No 7612271212537

Home > Modular DIN Rail Products > Mini Circuit breakers



Representative Image

The S802C-K16 is a 2-pole High Performance Circuit breaker with K-Characteristic, with cage terminal and a rated current of 16 A. It is a current limiting device with a maximum breaking capacity of 25kA at 240/415V. It can be used for voltages up to 254/440V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S802C-K16 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S802C-K16 more comfortable. Due to the fast arc extinction of S802C-K16 your application will be secured.

Descriptors

Category	Mini Circuit breakers
----------	-----------------------

Specifications

Interrupting Rating acc. to UL1077	(240 V AC) 20 kA (250 V DC) 10 kA
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 3.1 W
Product Main Type	S800C
Rated Current	16 A
Rated Ultimate Short-Circuit Breaking Capacity	(240 / 415 V AC) 25 kA (254 / 440 V AC) 15 kA (250 V DC) 10 kA
Rated Voltage (V)	(240 V AC) (480Y / 277 V AC) (250 V DC)
Standards	IEC/EN 60947-2 UL 1077
Tripping Characteristic	K