

Representative Image

Alternate Catalog No. X500-B4-48-XD
Catalog No. 3AUA0000226369

Description: PSTX ENCLOSED 500HP 480V TYPE4 XD

UPC No 6438177522461

Home > Soft Starters > Softstarter - Enclosed (PSTX)

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 600HP/720A, heavy duty class 30 starts for 500HP/590A, SSCR rating of 65kA, 480V and type 4 enclosure.

Descriptors

Category	Softstarter - Enclosed (PSTX)

Specifications

Enclosure Type	NEMA 4
Motor Voltage	480 V
Motor HP at 460V- Extreme duty	500
Protection Type	Circuit Breaker
Power Dissipation In Watts	240
Height (Inches)	72
Width (Inches)	36
Depth (Inches)	24

Dimensions

Weight (lb)	681
Height (mm)	1828,8
Depth (mm)	609,6
Weight (kg)	309