

Representative Image

# Alternate Catalog No. X200-B4-48-XD
# Catalog No. 3AUA0000226365

**Description: PSTX ENCLOSED 200HP 480V TYPE4 XD**

**UPC No 6438177522423**

**Home > Soft Starters > Softstarter - Enclosed (PSTX)**

PSTX extreme duty enclosed softstarters are the ultimate softstarting solution. Includes all features of the PSTX normal duty, sized for heavy duty applications, plus an AC-3 emergency bypass. Both the PSTX softstarter and TMAX XT breakers are utilized. Door mounted pilot devices include PSTX keypad, hand-off-auto selector switch, start and stop pushbuttons, power on pilot light, run pilot light, fault pilot light, normal/emergency bypass selector switch, emergency bypass start and stop pushbuttons and emergency bypass pilot light. Good for Normal Duty class 10 starts for 250HP/302A, heavy duty class 30 starts for 200HP/248A, SSCR rating of 65kA, 480V and type 4 enclosure.

## Descriptors

| | |
|---|---|
| Category | Softstarter - Enclosed (PSTX) |

## Specifications

| | |
|---|---|
| Enclosure Type | NEMA 4 |
| Motor Voltage | 480 V |
| Motor HP at 460V- Extreme duty | 200 |
| Protection Type | Circuit Breaker |
| Power Dissipation In Watts | 210 |
| Height (Inches) | 48 |
| Width (Inches) | 36 |
| Depth (Inches) | 16 |

## Dimensions

| | |
|---|---|
| Weight (lb) | 304 |
| Height (mm) | 1219,2 |
| Depth (mm) | 406,4 |
| Weight (kg) | 138 |